
ENG Laboratory Filtration





Membrane Filters Polivinildenedifloride PVDF

These filters are manufactured with Polivinildenedifloride polymer (PVDF). They are hydrophobic in nature and have a high temperature resistance. Dorsan ® also offers hydrophilic PVDF version. Designed to have high pressure resistance, flexibility and chemical compatibility. This membrane is highly valued for its ability to meet the highest requirements requested in the different applications of chemical filtration. Without the need for wetting agents this product is a good value alternative to PTFE membranes in applications to prevent moisture locking gas leaks or ventilation. Not recommended for use with acetone, DMF, DMSO or Bases > 6N.

Features

Hydrophobic or Hydrophilic version
Great chemical compatibility
Negligible protein binding
Low extractables
Autoclavable

Applications

Bacteria retention
Sample preparation for HPLC
Filtration of organic solvents
Ventilation
Clarification of biological solutions







Membrane filters Polivinildenedifloride PVDF specifications

Code	Description	Packaging u.				
0,20 μm						
M013PVDF020	PVDF Membrane Filter, Pore 0,20 (µm), Diameter: 13 mm	100				
M025PVDF020	PVDF Membrane Filter, Pore 0,20 (µm), Diameter: 25 mm	100				
M047PVDF020	PVDF Membrane Filter, Pore 0,20 (µm), Diameter: 47 mm	100				
M090PVDF020	PVDF Membrane Filter, Pore 0,20 (µm), Diameter: 90 mm	25				
M142PVDF020	PVDF Membrane Filter, Pore 0,20 (µm), Diameter: 142 mm	25				

0,45 μm	
PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 13 mm	100
PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 25 mm	100
PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 47 mm	100
PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 90 mm	25
PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 142 mm	25
	PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 13 mm PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 25 mm PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 47 mm PVDF Membrane Filter, Pore 0,45 (µm), Diameter: 90 mm

Note. Other dimensions or porosities should be available under request.

For Hydrophilic version, add PHIL at the end of the product code.

Technical characteristics

Pore size (µm)	Flow Time (s)	Volume/ Vacuum	Flow rate (ml/min/cm²	Bubble Point (psi)	Thickness (microns)	BSA protein binding capacity
0,22	100-500	250/20	3,18-15,91	40-60	140-250	70-80
0,45	35-200	250/20	7,95-45,45	25-40	140-250	60-70

